



### B-3 JIS Vプーリー - B・BX適用



単位: mm

品番	呼び径 dm	外径 de	最大軸穴径 d	下穴径 d <sub>2</sub>	形状 図番	ハブ				リム		慣性モーメント (kg・m <sup>2</sup> )	質量 (kg)
						d <sub>b</sub>	l	s <sub>1</sub>	s <sub>2</sub>	w	h <sup>+2</sup> <sub>0</sub>		
71-B-3	71	82	28	-	21U	50	45	15	33	63	20	0.00106	1.55
75-B-3	75	86	28	-	21U	50	45	15	33	63	20	0.00129	1.68
80-B-3	80	91	28	-	21U	50	45	15	33	63	20	0.00161	1.86
90-B-3	90	101	32	-	21U	56	45	15	33	63	20	0.0025	2.29
100-B-3	100	111	35.5	-	21U	63	45	15	33	63	20	0.00372	2.77
106-B-3	106	117	35.5	-	21U	63	45	15	33	63	20	0.00458	3.03
112-B-3	112	123	35.5	-	21U	63	45	15	33	63	20	0.00558	3.31
118-B-3	118	129	35.5	-	21U	63	45	15	33	63	20	0.00675	3.6
125-B-3	125	136	40	-	21U	71	50	15	28	63	20.5	0.00882	4.35
125-B-3F	125	136	40	-	41U	-	50	-	13	63	20.5	0.00944	4.7
132-B-3	132	143	40	-	21U	71	50	15	28	63	20.5	0.0108	4.76
132-B-3F	132	143	40	-	41U	-	50	-	13	63	20.5	0.0117	5.24
135-B-3	135	146	40	-	21U	71	50	15	28	63	20.5	0.0117	4.95
140-B-3	140	151	40	-	21U	75	50	15	28	63	20.5	0.0135	5.31
140-B-3F	140	151	40	-	40U	75	50	-	13	63	20.5	0.0112	4.28
145-B-3	145	156	40	-	21U	75	50	15	28	63	20.5	0.0154	5.64
150-B-3	150	161	40	-	21U	75	50	15	28	63	20.5	0.0175	5.97
150-B-3F	150	161	40	-	40U	75	50	-	13	63	20.5	0.014	4.58
155-B-3	155	166	40	-	21U	75	50	15	28	63	20.5	0.0197	6.32
160-B-3	160	171	40	-	21U	75	50	15	28	63	20.5	0.0222	6.67
160-B-3F	160	171	40	-	40U	75	50	-	13	63	20.5	0.0172	4.88
165-B-3	165	176	40	-	21U	75	50	15	28	63	20.5	0.0250	7.05
170-B-3N	170	181	45	-	20U	83	56	15	22	63	20.5	0.0217	5.76
170-B-3F	170	181	45	-	50U	83	56	-	3.5	63	20.5	0.0217	5.76
180-B-3N	180	191	45	-	20U	83	56	15	22	63	20.5	0.026	6.08
180-B-3F	180	191	45	-	50U	83	56	-	3.5	63	20.5	0.026	6.08
190-B-3N	190	201	45	-	20U	83	56	15	22	63	20.5	0.031	6.41
190-B-3F	190	201	45	-	50U	83	56	-	3.5	63	20.5	0.031	6.41



単位: mm

品番	呼び径 dm	外径 de	最大軸穴径 d	下穴径 d <sub>2</sub>	形状 図番	ハブ				リム		慣性モーメント (kg・m <sup>2</sup> )	質量 (kg)
						d <sub>b</sub>	l	s <sub>1</sub>	s <sub>2</sub>	w	h <sup>+2</sup> <sub>0</sub>		
200-B-3N	200	211	45	-	20U	83	56	15	22	63	20.5	0.0366	6.75
200-B-3F	200	211	45	-	50U	83	56	-	3.5	63	20.5	0.0366	6.75
212-B-3N	212	223	50	-	20X	91	63	15	15	63	20.5	0.0424	7.38
212-B-3F	212	223	50	-	50X	91	63	-	3.5	63	20.5	0.042	7.03
224-B-3N	224	235	50	-	20X	91	63	15	15	63	20.5	0.0506	7.77
224-B-3F	224	235	50	-	30X	91	63	-	-	63	20.5	0.0506	7.77
236-B-3N	236	247	50	-	20X	91	63	15	15	63	20.5	0.0593	8.08
236-B-3F	236	247	50	-	30X	91	63	-	-	63	20.5	0.0593	8.08
250-B-3N	250	261	50	-	20X	91	63	15	15	63	20.5	0.0708	8.45
250-B-3F	250	261	50	-	30X	91	63	-	-	63	20.5	0.0708	8.45
280-B-3N	280	291	50	-	20X	91	63	15	15	63	20.5	0.1	9.24
280-B-3F	280	291	50	-	30X	91	63	-	-	63	20.5	0.1	9.24
300-B-3N	300	311	50	-	20X	91	63	15	15	63	20.5	0.126	9.96
300-B-3F	300	311	50	-	30X	91	63	-	-	63	20.5	0.126	9.96
315-B-3	315	326	56	-	10X	100	71	8	-	63	20.5	0.148	11.4
355-B-3	355	366	56	-	10Y	100	71	8	-	63	21	0.232	13.8
375-B-3	375	386	56	-	10Y	100	71	8	-	63	21	0.275	14.4
400-B-3	400	411	56	-	10Y	100	71	8	-	63	21	0.336	15.2
450-B-3	450	461	56	-	10Y	100	71	8	-	63	21	0.484	16.9
500-B-3	500	511	63	-	10Y	112	71	8	-	63	21	0.679	19.7
560-B-3	560	571	63	-	10Y	112	71	8	-	63	21	0.962	21.7
600-B-3	600	611	63	-	10Y	112	71	8	-	63	21	1.19	23
630-B-3	630	641	63	-	10Y	112	71	8	-	63	21	1.41	24.8
710-B-3	710	721	63	16	10Y	112	71	8	-	63	21	2.07	28.4
750-B-3	750	761	63	-	10Y	112	71	8	-	63	21	2.45	29.8
800-B-3	800	811	71	33	10Y	125	80	17	-	63	21	3.06	34.7
850-B-3	850	861	71	33	10Y	125	80	17	-	63	21	3.68	36.7
900-B-3	900	911	71	33	10Y	125	80	17	-	63	21	4.49	40
950-B-3	950	961	71	33	10Y	125	80	17	-	63	21	5.29	42
1000-B-3	1000	1011	71	33	10Y	125	80	17	-	63	21	6.19	44

#### 追加工サービスをご利用ください。

Vプーリーに軸穴・キー溝・押しねじ穴の追加工をいたします。実働1日目出荷。



● 品番指定 ※価格・納期はNBKウェブサイトをご覧ください。

#### 300-B-3N



● 軸穴・キー溝・押しねじ追加工

対応可・別料金

#### ● 関連商品

プーリーV溝部の摩耗を確認するためのゲージがあります。プーリーのメンテナンスの際に、ご利用ください。

